

Lautsprecherkabel 2,5 mm² twinaxial highflex
Loudspeaker Cable 2,5 mm² twinaxial highflex

Stage
Economy



| Bestellnummer | Part No. | CLS 225 SW-GR |
|-----------------------------|----------------------------|--------------------------------------|
| Mechanische Daten | Mechanical data | |
| Leiterquerschnitt | Conductor area | 2,50 mm ² |
| Leiteraufbau | Composition of conductor | 140 x 0,15 mm CU blank / bare copper |
| Leiterisolation | Conductor isolation | PVC |
| Adernanordnung | Composition of cores | 2 verdrehte Adern / 2 twisted cores |
| Paarschirm / Schirm | Pair screen / screen | - |
| Gesamtmantel | Overall jacket | PVC mat, black-grey |
| Gesamtdurchmesser | Overall diameter | 7,8 +/- 0,2 mm |
| Gewicht | Weight | ca. 96 g/m |
| Betriebstemperatur bewegt | Working temperature mobile | (-5°C) - (+70°C) |
| unbewegt | fixed | (-20°C) - (+70°C) |
| Elektrische Daten | Electrical data | |
| Leiterwiderstand | Conductor resistance | 8 Ohm/km |
| Kapazität (Leiter / Leiter) | Capacity (cond./cond.) | - |
| Kapazität (Leiter / Schirm) | Capacity (cond./screen) | - |
| Prüfspannung | Test voltage | 2000 V eff. |