

Lautsprecherkabel 2,5 mm² twinaxial highflex
Loudspeaker Cable 2,5 mm² twinaxial highflex

Stage
Economy



Bestellnummer	Part No.	CLS 225 SW-GR
Mechanische Daten	Mechanical data	
Leiterquerschnitt	Conductor area	2,50 mm ²
Leiteraufbau	Composition of conductor	140 x 0,15 mm CU blank / bare copper
Leiterisolation	Conductor isolation	PVC
Adernanordnung	Composition of cores	2 verdrehte Adern / 2 twisted cores
Paarschirm / Schirm	Pair screen / screen	-
Gesamtmantel	Overall jacket	PVC mat, black-grey
Gesamtdurchmesser	Overall diameter	7,8 +/- 0,2 mm
Gewicht	Weight	ca. 96 g/m
Betriebstemperatur bewegt	Working temperature mobile	(-5°C) - (+70°C)
unbewegt	fixed	(-20°C) - (+70°C)
Elektrische Daten	Electrical data	
Leiterwiderstand	Conductor resistance	8 Ohm/km
Kapazität (Leiter / Leiter)	Capacity (cond./cond.)	-
Kapazität (Leiter / Schirm)	Capacity (cond./screen)	-
Prüfspannung	Test voltage	2000 V eff.