


Product information

Field Attachable M12 Connectors - Standard Type - RSC 4/7

Industrial Connecting Solutions:Circular Connectors:M8 - M12 Connectors:M12 Connectors:M12 Circular connector acc. to IEC 61076-2-101:M12 Field Attachable Connectors:Field Attachable M12

Connectors - Standard Type

http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256292-256304-58429-58478-58928/en/RSCG_4-7/ui/state

Name	
Field Attachable M12 Connectors - Standard Type	
	
Field attachable connector, M12 male connector, straight version, with threaded joint, assembling with screw terminals	
Delivery informations	
Availability	available
Product description	
Type	RSC 4/7
Order No.	11584
Description	Field attachable connector, M12 male connector, straight version, with threaded joint, assembling with screw terminals
Number of contacts	4
Color of housing	black
Classification	
Belden brand	Lumberg-Automation
Eclass-ID	27260702
Mechanical data	
Type of plug-in contact	Male connector
Design of housing	straight
LED display present	✘
Connectable conductor cross-section multiple wire (without sleeve)	max. 0.75 mm ²
Screw joint for cable for external cable diameter	3.0 mm ... 6.5 mm
Screwed cable gland, connecting thread	SW 15
Environmental conditions	
Environmental temperature	-25 °C ... 90 °C
Degree of protection (IP), mounted	IP67
Pollution degree	3
Materials	
Housing material / Molded body	PBT
Contact bearer material	PBT
Contact material	CuZn
Contact material - Surface refinement	pre-coppered, CuSnZn
Knurled screw / nut material	CuZn, nickel-plated
Sealing material	FKM
Electrical data	
Contact resistance	≤ 5 mΩ
Rated current In	4 A at 40°C, UL and notice derating
Nominal voltage	240 V
Rated voltage (Value)	250 V
Test voltage	2.0 kV eff./60 s
Insulation resistance	> 1 GΩ
Approvals	
Approvals	UL

Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.