




used for: D-SUB COMBINATION











NOTES:

1. METALSHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
   PLATING: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
   SOLDER CUP ACCEPTS CABLE AWG 20
4. CONNECTOR IS PART MARKED: 3009W4SCM99A10X CONEC Y/WW
5. [ ] = CRITICAL DIMENSION

Directive 2002/95/EC „RoHS" Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance

	date	name
2002		
drawn	09.08.	Parei
appd.	09.08.	Mickenbecker
norm		
d-old		

scale: 2:1 (5:1)

material: SEE NOTES

title:

D-SUB COMBINATION FEMALE

9W4S SOLDER CUP

dwg no: 13K1A673

AutoCAD 2000 | DIN-A 3 | sh: 1/1

part no: 3009W4SCM99A10X