

**PIN HEADER 2,54mm**

**ID: 088**

STL 1-XXXXA / STL 2-XXXXA / STL 3-XXXXA

Series 400

**TECHNICAL DATA**

Pitch	2,54 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	copper alloy
Rated Current	3 Amp.
Rated Voltage	150 V <sub>RMS</sub> /V <sub>DC</sub>
Withstanding Voltage	500 V <sub>AC</sub> for one minute
Operating Temperature	-40°C to +105°C
Maximum Soldering Temperature	260°C for 10 seconds

n = No. of Positions

Code	Dimensions		
	A	B	C
1130	11,30	3,50	3,30
1260	12,60	4,80	3,30
1390	13,90	6,10	3,30
1470	14,70	6,90	3,30
1770	17,70	9,90	3,30
1980	19,80	12,00	3,30
2160	21,60	13,80	3,30
2280	22,80	15,00	3,30
2490	24,90	17,10	3,30
Custom			

All dimensions in mm.  
Other dimensions upon request.

**STL X - XXXX A XX - XXX U**

Rows: 1 = 1 rows  
2 = 2 rows  
3 = 3 rows

Code: see table

A: right angled contacts

Plating: TT = Sn  
GT = Sel. Au  
GG = Au

U: RoHS-compliant with high temp. plastic

Pins: 1 row: 1 - 50 contacts  
2 rows: 2 - 100 contacts  
3 rows: 3 - 120 contacts

7 | 2,54 mm