


-40-55°C
 DC 30V 0.5A
 $\le 0.03\Omega$
 >100mA DC250V
 AC 500V (50Hz)/min
 3-20M
 5000次



4			IPC5	PA66 ()
3			IPC5	$\epsilon=0.20$
2			IPC5	H62 $\epsilon=0.35$
1			IPC5	$\epsilon=0.20$

KB 3 SPRK

A	B		1:1
1			1

TOLEBRANCE: UNLESS OTHERWISE SPECIFIED
 UNDER 1.5 ± 0.05 | 1.5 - 10 ± 0.1 | OVER 10 ± 0.2