



NO	DESCRIPTION	QTY	MATERIAL	PLATING
1	BODY 1	1	BRASS	GOLD 3-5 μ " MIN.
2	BODY 2	1	BRASS	GOLD 3-5 μ " MIN.
3	DIELECTRIC	1	TEFLON	-
4	CENTER PIN	1	PINSPR BRONZE	GOLD 10 μ " MIN.
5	FERRULE	1	BRASS	GOLD 3-5 μ " MIN.
6	PARTS	1	BRASS	GOLD 3-5 μ " MIN.

Dimensions Are In Millimeters
Unless Otherwise Specified

Tolerances

0.5-6	=	± 0.2
6-30	=	± 0.4
30-120	=	± 0.6
120-315	=	± 1.0
315-1000	=	± 1.6
1000-2000	=	± 2.4

RoHS COMPLIANT

0505024

P/N SC204CU-LGGT50

731092/0414036

SMC R/A CRIMP JACK
FOR RG316/U, RG174/U CABLE