


SCHEMATIC



Specification

Rating : 30VDC 0.5A
 Contact Resistance : <30Ω
 Insulation Resistance : >100MΩ
 Withstand Voltage : 500VAC (50/60Hz for 1 minute)
 Operation Force : 3 - 20N
 Operating Temperature : -20° ~ 70°
 Cycles Life : min. 5,000 times

Material BOM

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
8	HOUSING	1	PBT	
7	COVER	1	PBT	
6	AXIS SUPPORT	1	H59 BRASS	Ni-Plating
5	5#CONTACT FOOT	1	PHOSPHOR BRONZE	Ag-Plating
4	4#CONTACT FOOT	1	H62 BRASS	Ag-Plating
3	3#CONTACT FOOT	1	H62 BRASS	Ag-Plating
2	2#CONTACT FOOT	1	PHOSPHOR BRONZE	Ag-Plating
1	1#CONTACT FOOT	1	H62 BRASS	Ag-Plating

UNIT: MM	TYPE:	MODEL NO:	PAPER NO: A4	PAGE 1 OF 1		
	PHONE JACK	PJ-324M	TOLERANCE	ANGLES	SCALE	VER
			± 0.15	± 1.5°	3:1	1
DESIGNER BY:	Liu Xiaoheng		SUGO INDUSTRIAL COMPANY LIMITED			
CHECK BY:	Li Jian					
DATE:	2009-4-27					