



NYS238

3 pole 1/4" jack to jack adapter



Technical Information [hide](#)

Product

Title	NYS238
-------	--------

Electrical

Dielectric strength	0.5 kVdc
---------------------	----------

Insulation resistance	$\geq 1 \text{ G}\Omega$
-----------------------	--------------------------

Rated current	depends on mated connector
---------------	----------------------------

Contact resistance	depends on mated connector
--------------------	----------------------------

Mechanical

Lifetime	1000 mating cycles
----------	--------------------

Material

Insulation	ABS
------------	-----

Environmental

Temperature range	-25 °C to +70 °C
-------------------	------------------

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN
REAN a brand of Neutrik AG