



6	Terminals	Brass	Silver Ptd.	6
5	6P Housing	PBT		1
4	"T" Holder	Steel	Nickel Ptd.	1
3	Setscrew	Steel	Nickel Ptd.	1
2	Strain Boot	PVC		1
1	YE-147X Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications

rating : 100V AC 4A MAX
 contact resistance : pins-30mΩ MAX; shell-50mΩ MAX
 Insulation resistance : MIN 100 MEGΩ @500V DC
 voltage withstand : 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734408	DIN Stecker, 6-polig, Metallausführung