



|   |            |
|---|------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 890-122    |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.25 - 1.5 |
| <b>Cross section2 (Cross section / AWG)</b>                 | 22 - 16    |
| <b>Strip length (Strip length / mm)</b>                     | 9          |
| <b>Measured voltage (Measured voltage / V)</b>              | 250        |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4          |
| <b>Pollution degree (Pollution degree)</b>                  | 3          |
| <b>Current intensity (Current intensity / A)</b>            | 16         |
| <b>Height (Height / mm)</b>                                 | 13.2       |
| <b>Width (Width / mm)</b>                                   | 15.6       |
| <b>Depth (Depth / mm)</b>                                   | 61.6       |
| <b>COLOR (COLOR)</b>  | weiß       |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 5          |