



7	Terminals	Brass	Silver Ptd.	5
6	5P240 Housing	PBT		1
5	Strain Boot	PVC		1
4	Set screw	Steel	Nickel Ptd.	1
3	"T" Holder	Steel	Nickel Ptd.	1
2	YE-139X Cap	Zn Alloy	Nickel Ptd.	1
1	YE-139X Cover	Zn Alloy	Nickel Ptd.	1
<b>No.</b>	<b>Description</b>	<b>Material</b>	<b>Treat</b>	<b>Q'ty</b>

#### Specifications

rating :

100V AC 4A MAX

contact resistance :

pins-30mΩ MAX; shell-50mΩ MAX

insulation resistance :

MIN 100 MEGΩ @500V DC

voltage withstand :

250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734580	DIN Normstecker mit Renkverschluss, 5-polig, 240°