



7	Strain Boot	PVC		1
6	Terminals	Brass	Silver Ptd.	6
5	Housing	PA66		1
4	Setscrew	Steel	Nickel Ptd.	1
3	"T" Holder	Steel	Nickel Ptd.	1
2	Screw Cap	Zn Alloy	Nickel Ptd.	1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications

rating : 100V AC 4A MAX
 contact resistance : pins-30mΩ MAX; shell-50mΩ MAX
 insulation resistance : MIN 100 MEGΩ @500V DC
 voltage withstand : 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734594	DIN Normstecker mit Renkverschluss, 6-polig