



6	Contact Terminals	Brass	Silver Ptd.	4
5	4P Housing	PA66		1
4	Strain Boot	PVC		1
3	Setscrew	Steel	Nickel Ptd.	1
2	'T' Cable Holder	Steel	Nickel Ptd.	1
1	Shell Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications
rating : 100V AC 1A MAX
contact resistance :
 pins-30mΩ MAX; shell-50mΩ MAX
insulation resistance :
 MIN 100 MEGΩ @500V DC
voltage withstand :
 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734757	DIN Normkupplung mit Renkverschluss, 4-polig