



<b>ITEM-NO. (ITEM-NO.)</b>	890-222
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.25 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	22 - 16
<b>Strip length (Strip length / mm)</b>	9
<b>Measured voltage (Measured voltage / V)</b>	250
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	16
<b>Height (Height / mm)</b>	11.7
<b>Width (Width / mm)</b>	10.4
<b>Depth (Depth / mm)</b>	34.1
<b>COLOR (COLOR)</b>	weiß
<b>WEIGHT (WEIGHT / g)</b>	2