



6	Contact Terminals	Brass	Silver Ptd.	8
5	8P270 Housing	PA66		1
4	Strain Boot	PVC		1
3	Set screw	Steel	Nickel Ptd.	1
2	"T" Cable Holder	Steel	Nickel Ptd.	1
1	Shell Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

**Specifications**

rating :

100V AC 1A MAX

contact resistance :

pins-30mΩ MAX; shell-50mΩ MAX

Insulation resistance :

MIN 100 MEGΩ @500V DC

voltage withstand :

250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734824	DIN Normkupplung mit Renkverschluss, 8-polig, 270°