



4	3P Housing	PA66		1
3	Terminals	Brass	Silver Ptd.	3
2	Nagetive Contactor	Copper	Nickel Ptd.	1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications

rating :
100V AC 4A MAX
 contact resistance :
 pins-30mΩ MAX; shell-50mΩ MAX
 insulation resistance :
MIN 100 MEGΩ @500V DC
 voltage withstand :
250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734837	DIN Norm-Einbaubuchse mit Renkverschluss, 3-polig