



| 4 | 4P Housing | PA66 | | 1 |
|-----|--------------------|----------|-------------|------|
| 3 | Terminals | Brass | Silver Ptd. | 4 |
| 2 | Nagetive Contactor | Copper | Nickel Ptd. | 1 |
| 1 | Shield Cover | Zn Alloy | Nickel Ptd. | 1 |
| No. | Description | Material | Treat | Q'ty |

Specifications rating :

100V AC 4A MAX
contact resistance :
 pins-30mΩ MAX; shell-50mΩ MAX
Insulation resistance :
 MIN 100 MEGΩ @500V DC
voltage withstand :
 250V AC R.M.S. for 1 minute

| | |
|---------------|---|
| Artikelnummer | Artikeltext |
| 734849 | DIN Norm-Einbaubuchse mit Renkverschluss, 4-polig |