



Specifications rating :

100V AC 4A MAX
 contact resistance :
 pins-30mΩ MAX; shell-50mΩ MAX
 Insulation resistance :
 MIN 100 MEGΩ @500V DC
 voltage withstand :
 250V AC R.M.S. for 1 minute

4	5P 240 Housing	PA66		1
3	Terminals	Brass	Silver Ptd.	5
2	Nagetive Contactor	Copper	Nickel Ptd.	1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Artikelnummer	Artikeltext
734884	DIN Norm-Einbaubuchse mit Renkverschluss, 5-polig, 240°