


Crocodile clips

AGF 1



Product	AGF 1
description	Miniature alligator clip for small components, e.g. on printed circuits. silver-plated surface. Maximum clamping range 1 mm ² . Maximum connecting lead cross-section 0.5 mm ² solder or crimped.
operating instruction	BA210
Articlenummer	930476001 Ag
drawing	
	
technical data	
connection	solder connection, crimp terminal
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	3 A
material socket	brass, silver plated
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +100 °C
clamping range	1 mm

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022

2 mm system