



**Specifications**

rating : 100V AC 4A MAX  
 contact resistance : pins-30mΩ MAX; shell-50mΩ MAX  
 insulation resistance : MIN 100 MEGΩ @500V DC  
 voltage withstand : 250V AC R.M.S. for 1 minute

4	6P Housing	PA66		1
3	Terminals	Brass	Silver Ptd.	6
2	Nagetive Contactor	Copper	Nickel Ptd.	1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Artikelnummer	Artikeltext
735057	DIN Norm-Einbaubuchse mit Renkverschluss, 6-polig