




Product information GO 610 FA M schwarz/black

Industrial Connecting Solutions:Rectangular Connectors:DIN VDE 0627 / IEC 61984 Connectors (G serie):Cable plug:GO 610 FA M schwarz/black


<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24349-37031/en/conf/ui/state>

Name	GO 610 FA M schwarz/black
	
	Surface mounted connector with flange with solder contacts
Delivery informations	
Availability	available
Product description	
Description	Surface mounted connector with flange with solder contacts
Type	GO 610 FA M schwarz/black
Order No.	932 478-100
Type of contact	male
Number of contacts	6 + PE
Standard	DIN VDE 0627 / IEC 61984
Housing Color	black
Technical data	
Pin dimensions	1,6 mm (diameter)
Rated voltage	AC/DC 250 V
Rated current	DC 6 A / AC 10 A
Contact resistance	<= 4 mOhm
Type of termination	solder
Mounting	screws
Material	
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 V-1
Contact bearer	94 V-1
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Scope of delivery	1 surface mounted connector, 1 flat gasket
Accessories to order separately	can be plugged into GO 610 WF schwarz/black



Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2

58579 Schalksmühle

Germany

Phone: +49 7127/14-1806

E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.