



8	Terminals	Brass	Silver Ptd.	5
7	5P240 Housing	ABS		1
6	"T" Holder	Steel	Nickel Ptd.	1
5	Setscrew	Steel	Nickel Ptd.	1
4	Hook Button	Zn Alloy	Nickel Ptd.	1
3	Leaf Spring	Steel	Thermal Treatment	1
2	Strain Boot	PVC		1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1

Specifications rating :

100V AC 4A MAX
 contact resistance :
 pins-30mΩ MAX; shell-50mΩ MAX
 Insulation resistance :
 MIN 100 MEGΩ @500V DC
 voltage withstand :
 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
735404	DIN Stecker mit Verriegelung, 5-polig, 240°