



8	Terminals	Brass	Silver Ptd.	8
7	8P270 Housing	ABS		1
6	"T" Holder	Steel	Nickel Ptd.	1
5	Setscrew	Steel	Nickel Ptd.	1
4	Hook Button	Zn Alloy	Nickel Ptd.	1
3	Leaf Spring	Steel	Thermal Treatment	1
2	Strain Boot	PVC		1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1

**Specifications rating :**

100V AC 4A MAX  
 contact resistance :  
 pins-30mΩ MAX; shell-50mΩ MAX  
 Insulation resistance :  
 MIN 100 MEGΩ @500V DC  
 voltage withstand :  
 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
735467	DIN Stecker mit Verriegelung, 8-polig, 270°