



ITEM-NO. (ITEM-NO.)	2002-3227
Cross section1 (Cross section / mm²)	0.25 - 2.5 (4)
Cross section2 (Cross section / AWG)	22 - 12
Strip length (Strip length / mm)	10 - 12
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
Height (Height / mm)	69.5
Width (Width / mm)	5.2
Depth (Depth / mm)	93.5
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau