



SPECIFICATIONS:

1. CURRENT CARRYING CAPACITY :
 - 1) AC : 100V 1A MAX
 - 2) DC : 12V 2A MAX
2. CONTACT RESISTANCE : BEFORE TEST : 30m OHM MAX.
AFTER TEST : 80m OHM MAX
3. INSULATION RESISTANCE : BEFORE TEST : 50M OHM MIN. AT DC 250V.
AFTER TEST : 10M OHM MIN. AT DC 250V.
4. VOLTAGE WITHSTANCE : AC 250V 1 MINUTE.
5. INSERTION FORCE : BEFORE TEST : 1KG - 6KG
AFTER TEST : (1KG - 5KG)± 30%
WITHDRAWAL FORCE : BEFORE TEST : 0.8KG - 3.5KG
AFTER TEST : (0.8KG - 3.5KG)± 30%
6. LIFE TEST : 1000PCS CYCLES MIN. AT THE CONCLUSION OF THIS TEST, THE JACK
7. UNLESS OTHER SPECIFIED, TOLERANCE IS ± 0.2mm

Artikelnummer	Artikeltext
735718	Mini-DIN-Einbaubuchse, 4-polig, abgeschirmt
735731	Mini-DIN-Einbaubuchse, 5-polig, abgeschirmt
735743	Mini-DIN-Einbaubuchse, 6-polig, abgeschirmt
735755	Mini-DIN-Einbaubuchse, 7-polig, abgeschirmt
735767	Mini-DIN-Einbaubuchse, 8-polig, abgeschirmt