



ITEM-NO. (ITEM-NO.)	2091-1174
Cross section1 (Cross section / mm²)	0.2 - 1.5
Cross section2 (Cross section / AWG)	24 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	4
Height (Height / mm)	30
Width (Width / mm)	14
Depth (Depth / mm)	11.4
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	4
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 3,5 mm
Dimensions (Dimensions)	1.2 + 0.1 mm