

Plugs

MZS 2



Product	MZS 2
description	Injection-moulded adapter plug from 2 mm diameter plug to 4 mm diameter socket. This adapter plug enables application of 4 mm plugs and also sockets from 2 mm system.
operating instruction	BA208
article-no. / *colour	● 00 black ● 01 red Ni
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	6 A
material plug	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-20 °C to +60 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022