








B/N	Suplr's model No	Picture	DATA.	MATERIAL
736520	C5		Spring DIA:Φ3 Length/Trail distance : 130/98mm	Brass foundry
736473 / 736481	15#		Thickness of board:0.7mm Spring DIA:Φ2.5 Length/Trail distance : 104/76mm	Zinc plated
736503 / 736490	W1		Thickness of board:0.7 Spring DIA:Φ3.2 Length/Trail distance : 139/106mm	Zinc plated and Jaw is brass foundry
736546 / 736538	W2		Thickness of board:0.7 Spring DIA:Φ3.2 Length/Trail distance : 152.5/125mm	Zinc plated and Jaw is brass foundry
736554 / 736562	33#		Thickness of board:0.5 Spring DIA:Φ1 Length/Trail distance : 51.5/16.5mm	Nickel Plated
736597 / 736600	31#		Thickness of board:1.2 Spring DIA:Φ1.6 Length/Trail distance : 107/37.5mm	Nickel Plated
736589 / 736570	32#		Thickness of board:0.7 Spring DIA:Φ1.4 Length/Trail distance : 79/26mm	Nickel Plated