


**Specification**

Rating : 12 ~24VDC / 5A max.  
 Insulation Resistance : DC 500V 100Mohm min.  
 Voltage Breakdown : AC 1000V 1 minute  
 Operation Temperature : 0°C ~ 45°C  
 Fuse : 5A/250V  $\phi 6 \times 30$ mm glass tube



DATE	REVISION	APPROVAL BY	DIMENSION	mm $\pm 0.2$	PART No	HR2012
			DRAW BY	Camily	NAME	AUTO PLUG
			APPROVAL BY	Rikki	<b>SUGO INDUSTRIAL CO., LTD.</b> TEL : 852-27901280 FAX : 852-23890688 Email : sales@sugo.com.hk	
			DATE	03-12-2010		