

Housing design H-B. The industry standard.

Product Description

The smallest housing with single and double lever. The right housing is available for every application



Application range

- Plant engineering
- Light & sound technology
- Plastics industry

Benefits

- The smallest housing with single and double lever. The right housing is available for every application

Product features

- Hood, low version
- Bolts for double lever
- Straight cable entry
- Versions with / without neck



Technical Data

Material

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for double lever)					
10040000	H-B 10 TG 16		16	yes	10
10040100	H-B 10 TG 21		21	yes	10
19040000	H-B 10 TG M20	20			10
19040100	H-B 10 TG M25	25			10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.