


Housing design H-B. The industry standard.

Product Description

The housing standard. Wide choice for all applications



Application range

- Plant engineering
- Light & sound technology
- Plastics industry

Benefits

- The housing standard. Wide choice for all applications

Product features

- Cable coupler hood, low version
- Dual levers
- Straight cable entry
- Versions with / without neck



Technical Data

Material

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Neck	Pieces / PU
H-B housing: cable coupler hood (straight cable entry, double lever)					
10086000	H-B 16 TBF 21		21	yes	5
19086000	H-B 16 TBF M25	25			5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.