


A B C D E F G H

1

2

3

Maximum Electric Rating: 600V
 Maximum Electric Current
 22-16AWG/0.5-1.5mm²: 19A
 16-14AWG/1.5-2.5mm²: 27A
 12-10AWG/4-6mm²: 48A
 Shrinking Temperature: ≥150°C
 Operating Temperature: -40°C ~120°C
 Shrinking Ratio: 3:1
 Terminal Body: Copper
 Insulation: PE
 Plating: Tin



4

5

6

Wire Range mm ² /Awg	Item No.	Dimension(mm)			Insulation Color
		L	D	d2	
0.5-1.5mm ² 22-16AWG	341032SEL-TR	33.3	4.0	1.7	Transparent
0.5-1.5mm ² 22-16AWG	341032SEL	33.3	4.0	1.7	Red
1.5-2.5mm ² 16-14AWG	345040SEL	34.3	5.5	2.3	Blue
4-6mm ² 10-12AWG	343058SEL	41.0	6.4	3.4	Yellow

Heat Shrink Butt connector