


A B C D E F G H

1

2

3

Maximum Electric Rating: 600V  
 Maximum Electric Current  
 22-16AWG/0.5-1.5mm<sup>2</sup>: 19A  
 16-14AWG/1.5-2.5mm<sup>2</sup>: 27A  
 12-10AWG/4-6mm<sup>2</sup>: 48A  
 Shrinking Temperature: ≥150°C  
 Operating Temperature: -40°C ~120°C  
 Shrinking Ratio: 3:1  
 Terminal Body: Copper  
 Insulation: PE  
 Plating: Tin



4

5

6

Wire Range mm <sup>2</sup> /Awg	Item No.	Dimension(mm)			Insulation Color
		L	D	d2	
0.5-1.5mm <sup>2</sup> 22-16AWG	341032SEL-TR	33.3	4.0	1.7	Transparent
0.5-1.5mm <sup>2</sup> 22-16AWG	341032SEL	33.3	4.0	1.7	Red
1.5-2.5mm <sup>2</sup> 16-14AWG	345040SEL	34.3	5.5	2.3	Blue
4-6mm <sup>2</sup> 10-12AWG	343058SEL	41.0	6.4	3.4	Yellow

Heat Shrink Butt connector