

Innovative metal and plastic housing design

Product Description

Housing in plastic or metal version. For power supply in the smallest possible space



Application range

- Machine and equipment manufacturing
- Control engineering
- Electronic laboratory

Benefits

- Housing in plastic or metal version. For power supply in the smallest possible space

Product features

- Hood
- Bolts for single lever
- Straight cable entry
- Versions with / without cable gland



Technical Data

Material

Housing: grey thermoplastic, black Lever:
zinc-plated steel

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Material	Colour	Cable gland	Cable clamping range	Dimensions incl. cable gland	Pieces / PU
10425500	H-A 3 Tgv		11	Thermoplastic	black				10
10426000	H-A 3 Tgv		11	Thermoplastic	grey				10
10426700	H-A 3 Tgv		11	Thermoplastic	black	yes	6,5 - 12	62	10
10426400	H-A 3 Tgv		11	Thermoplastic	grey	yes	6,5 - 12	62	10
19425500	H-A 3 Tgv M20	20		Thermoplastic	black				10
19426000	H-A 3 Tgv M20	20		Thermoplastic	grey				10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.