

SPECIFICATIONS



Current Rating: 3 Amp

Insulation Resistance: 1000MΩ Min

Dielectric Withstanding: 600V AC/DC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C



MATERIALS

Contact Material: Phosphor Bronze


Insulation Material: Polyester, UL 94V-0

P.B.T or Nylon-6T

Contact Plating: Full Gold, Full Tin, Selective Plated

Standard: Gold Flash all Over Nickel




All materials must be RoHS compliant.



DIMENSIONS:

$L1 = 2.54 \times (\text{No. of Contacts} - 1)$

$L2 = 0.5 + 2.54 \times \text{No. of Positions}$



Recommended P.C.Board Layout

Datenblatt passend zu folgenden Artikelnummern

10120800 / 10120802 / 10120804 / 10120806