



Shellsize	A	B	C	ØD	E	F	G _{±0.3}	Cable Ø	Part-NO.
1	40.76	25.0	SW 22	24.6	51.0	22.0	77.0	5 - 10	165X14869X
2	49.06	33.3	SW 24	26.5	51.0	22.0	79.0	6 - 12	165X14879X
3	62.80	47.04	SW 24	26.5	59.5	22.0	87.5	6 - 12	165X14889X
4	78.86	63.5	SW 33	36.2	67.0	22.0	99.0	9 - 16	165X14899X
5	76.46	61.1	SW 42	47.0	67.0	24.8	107.0	13 - 20	165X14909X

Directive 2002/95/EC
 „RoHS“
 Compliant

NOTES:
 1. HOOD: PBT GF; BLACK
 2. SCREWS: STAINLESS STEEL

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY, WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		scale:	1:1		
	dim. in mm	material:	SEE NOTES		
2004	date	name	title:		
drawn	25.11.	Lehmenkühler	WATER RESISTANT D-SUB HOOD 9-50pos. with short screw		
appd.	25.11.	Mickenbecker			
norm					
	d-old		dwg no:	AutoCAD 2004	DIN-A
CONEC			16K1A1289	3	sh: 1/1
			part no:	SEE TABLE	