


Minimum cable  $\phi$ :  $\phi_{Fmin}=3,0$   
 Maximum cable  $\phi$ : - with rubber bushing :  $\phi_{Fmax}=6,5$   
 - without rubber bushing :  $\phi_{Fmax}=9,5$

09 67 009 0349	M3
09 67 009 0344	4-40 UNC
Part number	jack screw thread

33112	28/09/05	JMDR
32329	15/11/04	TR
Mod.	Dat.	Name

	Dat.	Name
Detail.	15/11/04	TR
Insp.		
Stand.		
HARTING EURL F-95972 Paris		



All Dim. in mm  
Orig. Size DIN A 3

D-Sub hood 9 poles top entry, full metal hood with short jack screw		Maßstab/ Scale
		1,5:1
TB 09 67 009 034X		Blatt/ Page
Sub. TB 09 67 009 0344 / TB 09 67 009 0348		2 / 4