



## SPECIFICATIONS

**Current Rating:** 1.0 Amp

**Dielectric Withstanding:** 500V AC

**Insulation Resistance:** 3000M $\Omega$  Min

**Contact Resistance:** 30m $\Omega$  Max.

**Operating Temperature:** -40 $^{\circ}$ c to +105 $^{\circ}$ c

## MATERIALS

**Insulation Material:** P.B.T, UL 94V-0

**Contact Material:** Phosphor Bronze or Brass

**All materials must be RoHS compliant.**

No. of Contacts	Dimensions(mm)		
	A	B	C
06	12.30	5.08	3.80
08	14.84	7.62	1.80
10	17.38	10.16	3.80
12	19.92	12.70	3.80
14	22.46	15.24	3.80
16	25.00	17.78	3.80
18	37.54	20.32	3.80
20	30.08	22.86	3.80
24	35.16	27.94	3.80
26	37.70	30.48	3.80
30	42.78	35.56	3.80
34	47.86	40.64	3.80
36	50.40	43.18	3.80
40	55.48	48.26	3.80
50	68.18	60.96	3.80
60	80.88	73.66	3.80
64	85.93	78.74	3.80

Datenblatt passend zu folgenden Artikelnummern
10120858 / 10120862 / 10120864
10120111 / 10120112 / 10120113 / 10120114 / 10120115 / 10120116 / 10120117