




Rating	10A 35V AC/70V DC
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Red/Black



Color	SCI BOM No.
Red	1540626
Black	1540627

							△
							△
Date		Name		Description		NO	
Drawn	Checked	Approved	SCI BOM No.	SEE TABLE	Model Name	DUAL TEST ADAPTER	
			Customer No.		Model No.	R8-84	
			Unit	mm		REV.	
						0	