


Rating	10A 35V AC/70V DC
Contact Resistance	DC 500V 100M ohm Min.
Insulation Resistance	AC 1200V 1 minute
Operation Temperature	-20°C~80°C
Color	Red/Black



Color	SCI BOM No.
Red	1540622
Black	1540623

									△	
									△	
Date	Name	Description							NO	
Drawn	Checked	Approved	SCI BOM No.	See Table	Model Name	Banana Plug				
			Customer No.		Model No.	R8-20A			REV.	
			Unit	mm						0