

**W-Series, Accessories**  
**WAP WDK2.5****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal. Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

**General ordering data**

Type	WAP WDK2.5
Order No.	<a href="#">1059100000</a>
Version	W-Series, Accessories, End plate
GTIN (EAN)	4008190101954
Qty.	20 pc(s).

## W-Series, Accessories WAP WDK2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	69 mm	Width	1.5 mm
Height	54.5 mm	Net weight	4.587 g

### Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

### Additional technical data

Installation advice	Feed-through (bushing), Direct mounting	Version	End plate
---------------------	--	---------	-----------

### Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

### System specifications

Product family	W-Series, Accessories
----------------	-----------------------

### Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

### Approvals

ROHS	Conform
------	---------

### Downloads

STEP	<a href="#">1059100000_12456_WAP_WDK2.5_STP.stp</a>
<a href="#">3D Modell</a>	