



**NEUTRIK**

**NYS322G**



DIN male cable connector, 5-pole, gold plated contacts

**Product**

Connector Type           DIN  
Gender                     male

**Electrical**

Contact resistance       < 10 mΩ  
Dielectric strength       0,5 kVdc  
Rated current per contact depends on mated connector A

**Mechanical**

Cable O.D.               ≤ 5 mm  
Wire size                 26 AWG

**Material**

Bushing                 PVC  
Contact plating         0.2 μm Au  
Contacts                Brass (CuZn39Pb3)  
Insert                   Polyamide (PA 6 30 % GR)  
Shell                    Zinc diecast (ZnAl4Cu1), gal Ni plated  
Strain relief            CRIMP type zn plated

**Environmental**

Solderability           Complies with IEC 68-2-20  
Temperature range      -20 °C to +70 °C