







5

4



3

2

1



1) Markierung erster Kontakt, Ader 1 des Flachkabels
 1) Contact no.1, 1st wire of flat cable
 1) Contact no.1, repère 1 du câble

		 All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse/ Free size tolerances	
A	09185065813	0,76 μm Au			Detail.	Dat.	Name	2:1	SEK 18 Female connector 6 poles with central polarisation without cable stop with strain relief
	09185066813	2			Insp.	01-FEB-00	JMV		
	09185067813	3			Stand.				
	Bestell-Nr. Part-No. Reference	Anforderungsstufe performance level Niveau de qualite							
			26570	01-FEB-00	JB	HARTING EURL F-95972 Paris		 TB 0918506X813 Sub.	Blatt/ page 1/1
			Mod.	Dat.	Name				