

**Terminal markers  
ESO 7 A4-BOGEN WEISS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The various connector markers from Weidmüller enable users to solve virtually every labelling task on all types of lines. Whether several lines of labelling, ready-to-use markers with standard printing, or individual labelling, whether white or coloured markers or common designations at the clamping points, the comprehensive range of products represent the easy, quick and clear answer to every marking task.

**General ordering data**

Type	ESO 7 A4-BOGEN WEISS
Order No.	<a href="#">1607720000</a>
Version	Terminal markers, 27 x 6.3 mm, Paper, Colour: White
GTIN (EAN)	4008190206116
Qty.	10 pc(s).

**Terminal markers  
ESO 7 A4-BOGEN WEISS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**
**Dimensions and weights**

Length	27 mm	Width	6.3 mm
Height	1 mm	Net weight	10.5 g

**General data**

Colour	White	Material	Paper
Material colour according to resistance code	9	Number per sheet	240
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB		

**Connector markers**

Pitch in mm (P)	7 mm
-----------------	------

**Classifications**

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

**Approvals**

Approvals	
ROHS	Conform

**Downloads**

M-Print® PRO configuration file	<a href="#">lab_eso_7_din_a4_mcf.zip</a>
---------------------------------	--