




Max wire ϕ 1,05 mm



D
C
B
A

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, Male, Straight, 15 poles with turned solder buckets and hole	Maßstab/ Scale 1.5:1
						Detail.	18/07/01	AF			
09 67 015 5615.05	3.1 ^{+0,1}	S4				Insp.					
09 67 015 5615.00	3.1 ^{+0,1}	2				Stand.					
09 67 015 5604.00	3.1 ^{+0,1}	3									Blatt/ Page 1 / 1
			29700	18/07/01	AF	HARTING EURL F-95972 Paris			TB 096701556xx		
Part number	Ø hole	Performance level	Mod.	Dat.	Name				Sub.		