



5

4


3

2

1



Max wire ø 1,05 mm





D

C

B

A

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, Female, Straight, 15 poles with turned solder buckets and hole	Maßstab/ Scale 1.5:1
						Detail.	18/07/01	AF			
09 67 015 4715.05	3.1 <sup>+0,1</sup>	S4				Insp.					
09 67 015 4715.00	3.1 <sup>+0,1</sup>	2				Stand.					
09 67 015 4704.00	3.1 <sup>+0,1</sup>	3									Blatt/ Page 1 / 1
			29700	18/07/01	AF	HARTING EURL F-95972 Paris			TB 096701547xx		
Part number	ø hole	Performance level	Mod.	Dat.	Name	Sub.					