

## Double-level terminal block - UKK 5 - 2774017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Double-level terminal block, Cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 24 - 12, Connection type: Screw connection, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15, NS 32

### Product Features

- Large-surface labeling option

### Key commercial data

package_quantity	50
GTIN	4017918068301

### Technical data

#### General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

#### General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I <sub>N</sub>	32 A
Nominal voltage U <sub>N</sub>	500 V
Open side panel	ja

#### Dimensions

Width	6.2 mm
Length	56 mm
Height NS 35/7,5	62 mm
Height NS 35/15	69.5 mm
Height NS 32	67 mm

#### Connection data

## Double-level terminal block - UKK 5 - 2774017

### Technical data

#### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.2 mm <sup>2</sup>
2 conductors with same cross section, solid max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.2 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm <sup>2</sup>
Cross section with insertion bridge, solid max.	4 mm <sup>2</sup>
Cross section with insertion bridge, stranded max.	2.5 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

### classifications

#### eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

# Double-level terminal block - UKK 5 - 2774017

## classifications

### ETIM

<b>ETIM 2.0</b>	EC000897
<b>ETIM 3.0</b>	EC000897
<b>ETIM 4.0</b>	EC000897
<b>ETIM 5.0</b>	EC000897

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## approvals

CSA / UL Recognized / KEMA-KEUR / cUL Recognized / GL / DNV / RS / PRS / CCA / cULus Recognized /

### Approval details

<b>CSA</b>		
<b>Usegroups</b>	<b>B</b>	<b>C</b>
Nominal voltage UN	300 V	300 V
Nominal current IN	25 A	25 A
mm <sup>2</sup> /AWG/kcmil	28-10	28-10

<b>UL Recognized</b>	
Nominal voltage UN	600 V
Nominal current IN	30 A
mm <sup>2</sup> /AWG/kcmil	26-10

<b>KEMA-KEUR</b>	
Nominal voltage UN	500 V
Nominal current IN	32 A
mm <sup>2</sup> /AWG/kcmil	4

# Double-level terminal block - UKK 5 - 2774017

## approvals

<b>cUL Recognized</b>	
Nominal voltage UN	600 V
Nominal current IN	30 A
mm <sup>2</sup> /AWG/kcmil	26-10

**GL**

**DNV**

**RS**

**PRS**

<b>CCA</b>	
Nominal voltage UN	500 V
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	4

**cULus Recognized**

## accessories

### Partition plate

DP-UKK 3/5 - 2770794



## Double-level terminal block - UKK 5 - 2774017

### accessories

TS-KK 3 - 2770215



---

### End cover

DG-UKK 3/5 - 2770817



D-UKK 3/5 - 2770024



---

### Warning label printed

WS 5- 6 - 1004403



WS 4- 6 - 1004209



## Double-level terminal block - UKK 5 - 2774017

accessories

WS 3- 6 - 1004115



---

### Bridge

FB-150 METER - 0201595



---

LB 10-6 BU - 0202280



---

LB 10-6 RD - 0202293



---

LB 10-6 GY - 0202358



## Double-level terminal block - UKK 5 - 2774017

### accessories

LB 100-6 GY - 0202345



LB 100-6 RD - 0202316



LB 100-6 BU - 0202303



FBI 10- 6 - 0203250



FBI 20- 6 - 0201867



FBI 100- 6 - 0201650



## Double-level terminal block - UKK 5 - 2774017

accessories

---

EB 2- 6 - 0201155



EB 3- 6 - 0201142



EB 10- 6 - 0201139



SBRN 2-7 - 1413230



USBR 2-7 - 2303239





## Double-level terminal block - UKK 5 - 2774017

### accessories

USBRJ 2-7 - 2305538



---

### Short-circuit connector

KSS 3- 6 - 0309523



KSS 6 - 0301547



---

### Test plug terminal block

PS-UKK 5 - 3000625



PS-UKK/E - 3000641



## Double-level terminal block - UKK 5 - 2774017

accessories

RPS - 0201647



---

### Partition plate

ATP-UKK 3/5 - 2778521



---

### Terminal marking

SBS 6:UNBEDRUCKT - 1007222



ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



## Double-level terminal block - UKK 5 - 2774017

### accessories

UCT-TM 6 - 0828736



---

### Insulating sleeve

IS-K 4 - 1302338



---

ISSBI 10- 6 - 0301505



---

### Mounting rail

NS 32 PERF 2000MM - 1201002



---

NS 32 UNPERF 2000MM - 1201015



## Double-level terminal block - UKK 5 - 2774017

### accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



## Double-level terminal block - UKK 5 - 2774017

accessories

---

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



## Double-level terminal block - UKK 5 - 2774017

### accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



## Double-level terminal block - UKK 5 - 2774017

accessories

---

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



**Labeled terminal marker**

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



**End block**

---

## Double-level terminal block - UKK 5 - 2774017

### accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



**Test socket**



## Double-level terminal block - UKK 5 - 2774017

### accessories

PSBJ 3/13/4 - 0201304



PSB 3/10/4 - 0601292



### Drawings

Circuit diagram

