

Circular connectors for Servo Cables and encoders

### Product Description

Housings are very flexible - cable connectors with wide clamping range, receptacle housings for assembling the inserts from the front and rear



### Application range

- Plant engineering
- Servo drives and servo assemblies
- Measurement and control technology

### Benefits

- Housings are very flexible - cable connectors with wide clamping range, receptacle housings for assembling the inserts from the front and rear

### Product features

- Cable connector



Technical Data

Material

Housing: nickel-plated zinc die-casting Sealing:  
FPM

Protection rating

IP68 (10h / 1m)

Temperature range

-25°C - +125°C

VDE-tested

Certified production control: VDE-REG. no. 24

Article List

Part number	Article	Coding	Cable clamping range	Pieces / PU
Type M23 D6 cable connector				
44420037	M23 D6	black (N)	7 - 13,5	5
72044030	M23 D6	black (N)	7 - 10	5
72044020	M23 D6	black (N)	7 - 10	20
72044000	M23 D6	black (N)	9,5 - 13,5	5
72044010	M23 D6	black (N)	9,5 - 13,5	20
44420038	M23 D6	red (+20°)	7 - 13,5	5
72044230	M23 D6	red (+20°)	7 - 10	5
72044220	M23 D6	red (+20°)	7 - 10	20
72044200	M23 D6	red (+20°)	9,5 - 13,5	5
72044210	M23 D6	red (+20°)	9,5 - 13,5	20
44420036	M23 D6	blue (-20°)	7 - 13,5	5
72044130	M23 D6	blue (-20°)	7 - 10	5
72044120	M23 D6	blue (-20°)	7 - 10	20
72044100	M23 D6	blue (-20°)	9,5 - 13,5	5
72044110	M23 D6	blue (-20°)	9,5 - 13,5	20

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.