


| CONNECTOR FEATURES | |
|------------------------|---------------------------------------|
| PRODUCT TYPE | DIN43650/A CONNECTOR FIELD ATTACHABLE |
| HOUSING COLOUR | BLACK |
| HIGH HOUSING | 30mm |
| TYPE CONTACTS | SCREW WITH CONDUCTOR PROTECTION |
| CONTACT SPACING | 18mm |
| NUMBER OF POLES | 3POLES+EARTH |
| CABLE EXIT | PG9/PG11 UNIFIED |
| MAXIMUM CONDUCTOR SIZE | 1.5mm |
| FIXING SCREW | M3X32.5 |
| PROFILED GASKET | NBR |
| PROTECTION CLASS | IP67 |
| CIRCUIT TYPE | WITHOUT ELECTRONIC |
| VOLTAGE | 1-250V AC/DC |

| TOLLERANZE | DISGNATORE | DATA | SCALA | PE30 |
|------------|-------------------------------|----------|-------|------|
| UDM | LORENZO CHINNO CONTROLLATO | 20-12-10 | 1 : 1 | |

| DESCRIZIONE | TIPO | MATERIALE |
|---|------|-----------|
| CONNECTOR DIN43650/A G1 SERIES CONTACT SPACING:18mm,3P+E, BLACK HOUSING, WITHOUT ELECTRONIC,PG9/11 UNIFIED | G1 | |


H.T.P.
 HIGH TECH PRODUCTS

G1NU3000